

# MaxiMizer

Easy to use dispensers with lockable chemical cabinets

A complete range of, user-friendly dispensers for up to 5 products. Lockable cabinets ensure security of chemical products and safety of users.

Thanks to chemically-inert components, wipe clean surfaces and the ability to lock away the cleaning products, MaxiMizer is suitable for the cleaning and sanitisation of all locations including: kitchens, restaurants, schools, hotels, hospitals, care homes, food plants and many more.

- Dilutes and dispenses up to 5 products, in 5 l. bottles
- Hot water compatible (up to 65° C)
- Will handle variable pressure 1.5 - 6 Bar
- Flow rates: low flow 4 lit./min.; high flow 14 lit./min. (Low flow - bottle filling, high flow - bucket filling)
- Standard Dilution range: Low flow, from 3:1 to 125:1 (25% - 0.77%); High flow, from 3:1 to 350:1 (25% - 0.28%)
- Ultra-lean tips for up to 950:1 (0.10%) dilution and special devices up to 1300:1 (0.08%) for super-concentrates
- Huge choice - 19 models available, and options to customise with own colours, buttons and labels



often Used



schools  
universities



fast food  
facilities



fine dining



hotels &  
lodging



healthcare



food retail



transportation



carwash &  
auto detailing



food  
processing



pet care

# Further Information



Number of Products	Backflow prevention		No. of Products		Approx. Dilution range H2O : Chem.	
	Air Gap (DC)	E-Gap (DB)	4 lit./min.	14 lit./min.	4 lit./min.	14 lit./min.
1 Product Models (Either low flow or high flow, choice of dilution)	2830GBA-2	28301GB	1		3:1 to 125:1	
	2833GBA-2	28331GB		1	3:1 to 350:1	
1 Product Models (Both low flow and high flow, choice of dilution)	2848GBA-2	28481GB	1	1	3:1 to 125:1	
	2841GBA-2	28411GB	2		3:1 to 125:1	
2 Product Models (Choice of dilution and flow rate for each product)	2844GBA-2	28441GB	2		3:1 to 350:1	
	2846GBA-2	28461GB	1	1	3:1 to 125:1	
	2850GBA-2	28501GB	3		3:1 to 125:1	
3 Product Models (Choice of dilution and flow rate for each product)	2853GBA-2	28531GB	3		3:1 to 350:1	
	2856GBA-2	28561GB	1	2	3:1 to 125:1	
	2858GBA-2	28581GB	2	1	3:1 to 125:1	
	2860GBA-2	28601GB	4		3:1 to 125:1	
4 Product Models (Choice of dilution and flow rate for each product)	2864GBA-2	28641GB	1	3	3:1 to 125:1	
	2865GBA-2	28651GB	2	2	3:1 to 125:1	
	2866GBA-2	28661GB	3	1	3:1 to 125:1	
	2867GBA-2	28671GB	4		3:1 to 350:1	
Select Four (4 products, all low flow or all high flow, with choice of dilution for each)	2874GBA-2	28741GB	4		3:1 to 350:1	
	2875GBA-2	28751GB	4		3:1 to 125:1	
Select Four Plus (5 products; 4 low flow plus 1 high flow, each with choice of dilution)	2876GBA-2	28761GB	4	1	3:1 to 125:1	
Compact Four (4 products, all low flow, in a compact cabinet, max 2.5L. bottles)		28621GB			3:1 to 125:1	